Apogee[™] Bake Plate

With DataStream[™] Technology

Cee[®] Apogee[™] Bake Plate features a revolutionary intuitive interface, a space-saving design, and track-quality thermal accuracy and uniformity.

Serving the Semiconductor Industry Since 1987

BENEFITS

• Compact design for minimized footprint

Cost Effective Equipment

- Full-color, 7-inch touch screen display
- Durable benchtop design That is also available in a flange/ deck mountable configuration
- Enhanced logging
- Cool touch exhausted hood
- Smart Pins for programmable height control
- Adjustable exhaust gate
- DataStream[™] technology

BAKE HOOD DESIGN

- All-stainless-steel construction
- Unique 2-layer design reduces exterior hood temperature
- Exhausted hood for removal of process chemicals
- Optional nitrogen purge for inert bake environment

PROGRAMMABILITY

- Touch screen interface and display
- Full-color alphanumeric-capable graphical user interface (GUI)
- A virtually unlimited number of user-defined recipe program steps
- 0.1-s resolution for step times with a range of 0 to 9,999.9 s/step
- Virtually unlimited recipe storage
- Four automated bake methods: contact, vacuum, proximity, and lift pins
- Bake plate auto-sizing for 2- inch, 3-inch, 100-, 150-, and 200-mm substrates
- Temperature data recording
- Smart Pins programmable in 0.1-mm increments with an overall range of 0 to 19 mm
- Connectivity: USB/Ethernet port for communications for uploading/downloading process parameters with DataStream[™] technology



PRECISION

- Substrate sizes: up to 200 mm round; 8 inches × 8 inches square
- Temperature resolution: 0.1°C
- Temperature range: ambient to 300°C (400°C optional)
- Temperature uniformity: 0.3% across working surface

RELIABILITY

- Exceptional uptime
- 1-year full warranty on parts and labor
- Free remote technical support (phone, email, fax) for the life of the product
- Application process assistance for the life of the product

CostEffectiveEquipment.com (573) 466-4300

UTILITIES

- Voltage ranges: 100, 110-125, 208-240 VAC
- Power requirements: 1683 watts (max)
- Exhaust port: 2 inch OD
- Vacuum: 20 inches Hg
- Exhaust: 5 to 10 cfm
- N_2 (for bake plate proximity): 35 psi

DIMENSIONS

• 13.25" (33.65cm) W \times 21" (48.26cm) D \times 17.25" (30.48cm) H

- Machine weight: 65 lb (29.5 kg)
- Shipping weight: 148 lb (67.1 kg)

DATASTREAM™ TECHNOLOGY: CONNECTING THE SEMICONDUCTOR INDUSTRY

DataStream[™] technology gives you access to all of your connected Apogee[™] manufacturing equipment in one place to track, access, and modify your systems via a web browser. This technology will give manufacturers the ability to process and visualize data in real time and search and export that data into a number of different formats.

Real-Time Process Information

- Constant feedback of process information for monitoring critical process parameters
- Streamlined interface between different tool types
- Visual cues on process status & health

Advanced Recipe Creation

- Seamless switching between basic and advanced recipe creation methods
- Plain-English recipe translation
- Pre-defined process commands
- Unlimited process steps
- Unlimited recipe storage

Environmental Monitoring

- Monitoring of temperature & humidity allows for stricter control of critical processes
- Set preconditions and tolerances for monitored parameters
- On-screen, colored visual cues for deviation from controlled specs

Data Logging & Export

- Export data logs into commonly readable formats for further analysis and process troubleshooting
- Increase process efficiency
- Identify process control deviations
- Analyze multiple processes for best known method (BKM) development

© 2019 Cost Effective Equipment, LLC.

All statements, technical information, and recommendations contained herein are based on tests we believe to be accurate, but the accuracy or completeness thereof is not guaranteed and the following is made in lieu of warranty expressed or implied. Neither the seller nor the manufacturers shall be liable for any lipury, loss; or damage, direct or consequential, arising from the use or inability to use the product. Before using, user shall determine the suitability of the product for his intended use, and user assumes all risk and liability whatsoever in connection therewith. No statement or recommendation contained herein shall have any force or effect unless in an agreement signed by officers of the seller and manufacturer.

Effective Date: 4/1/2019